SOUNDCAM 3



Acoustic camera: powerful, intuitive, versatile



Typical applications

Check soundproofing

Localizing occupational noise

 Z_{C}

Sound emission from devices and systems

4

Diagnosis of electronic devices

= :=

Pinpointing environmental noise

Hardware High-performance

The **SoundCam 3** is an acoustic camera with outstanding performance features. The large number of microphones ensures high-resolution images with very high dynamic range. Even weak sound sources can be made visible in the presence of strong sources. The microphone data is analyzed in real time. Simultaneous data from the optical and thermal imaging cameras, as well as other sensors, ensure optimum information acquisition. In addition to the standard mode, which is very easy to operate, and the Pro mode, which is used for very demanding analyses, further operating modes are implemented for special measurement tasks. Customized operating modes can be created very easily and placed on the start screen.

The device is very robust and works even under extreme conditions. Thanks to the IP54 protection class, it can also be used in humid environments. The four integrated LEDs make it possible to work in the dark without external lighting. However, the SoundCam 3 is not only a superior measuring device, but with the help of the Windows software it is also a comprehensive tool for easily evaluating the measurement data.

- Extremely high dynamic range and accuracy thanks to the optimized array with 176 microphones and 200 kHz sampling rate at 24 bit resolution
- » Wide frequency range for more sensitive detection and better noise suppression
- » High frame rate of the acoustic video for the detection of transient noise
- » Synchronization between acoustic and optical video for high analysis accuracy
- » Global shutter and high frame rate of the optical video for fast-moving objects or fast movements
- » Simultaneous acquisition and recording of the acoustic, optical and thermal image
- » Optimum match of camera and display resolution through pixel-identical playback
- » Very good readability and high color transmission of the display thanks to optical bonding, even in bright sunlight





| Hardware | | |
|-------------|----------------------|--|
| Microphones | | 176 digital MEMS microphones |
| microphones | Frequency range | Up to 90 kHz |
| | Sample rate | 200 kHz |
| | Sound pressure | Max. 120 dB |
| | Resolution | 24 bit |
| | Beamforming | 100 fps |
| Ontical | Resolution | 1280 x 800 px at 40 fps |
| | Illumination | 4 LEDs |
| | Aperture angle | 74° x 51° (FoV horizontal x vertical) |
| | Shutter | Global shutter |
| | Night vision | Yes (external IR illumination recommended) |
| Thermal | Sensor Technology | Uncooled microbolometer |
| | Spectral Range | Longwave infrared, 8 µm to 14 µm |
| | Resolution | 160 x 120 progressive scan |
| Camera | Frame Rate | 8,7 fps |
| | Sensitivity | <50 mK (0,050°C) |
| | TCompensation | Automatic |
| | Measuring Range | -10° to +140°C with +/-5°C or 5% |
| | and Accuracy | -10° to +400°C with +/-10°C or 10% |
| | and Accuracy | Larger value is to be applied |
| | Aperture angle | 57° x 44° (FoV horizontal x vertical) |
| | Temperature unit | Kelvin, Celsius, Fahrenheit |
| Dienlou | | 7 inch |
| Display | Resolution | 1280 x 800 px |
| | Brightness | Adjustable |
| | 3 | • |
| | Readability Touch | Excellent through optical bonding Capacitive 10-finger touch |
| Fresh addad | Internal memory | 1TB M.2 SSD |
| Controller | | Linux |
| Interfaces | | |
| interraces | Ethernet | Data export |
| | | Remote control and data export |
| | Audio | 3,5 mm port for headphones |
| Dl | USB-C | Charging, remote control and data export |
| | Dimensions | 34 x 34 x 10 cm / 13,4 x 13,4 x 3,9 inch |
| Properties | | 2,6 kg / 5,7 lb |
| | Protection class | IP54 waterproof |
| | Operation | Two-, one-handed, shoulder strap, tripod |
| | Battery life | 3,5 h |
| | Bat. charging time | 1,5 h |
| | Tripod socket | 1/4 inch |
| | Buttons | 8 configurable + on/off switch |
| | Operating temp | -15°C to 50°C / 5°F to 122°F |
| | Charging temp | 0°C to 45°C / 32°F to 113°F |
| | Storage temp | -30°C to 60°C / -22°F to 140°F |
| Power | Built-in battery | Li-ion battery (48 Wh) |
| | Input | 20 V via USB C |
| | Management | Smart: use and charge at the same time |

Software Comprehensive and intuitive

The **SoundCam 3** software is intuitive and very easy to use. Very useful measurement modes allow you to work quickly and efficiently. These have preset parameters so that any user can carry out the measurements without prior knowledge. The device starts the measurement at the touch of a button and finds the acoustic source very quickly. Helpful functions such as long-term measurement and the trigger function enable automated measurement. In long-term measurement mode, noise sources can be found over a defined period of time. The trigger function automatically measures sporadic events without the presence of a measurement technician. The measurement is triggered via the level or a defined trigger curve and then saved. The measurement data can be analyzed and evaluated using the identical PC software. The software package for the SoundCam 3 is extremely high-performance, user-friendly, inclusive and license-free.

- » Four modes with preset parameters: Standard, Pro, Leakage and Partial discharge
- » Live, on-screen results at 100 acoustic fps
- » Three acoustic scaling modes
 - » Smart: Suppression of background noise
 - » Auto: Dynamic scaling
 - » Manual: Comparison with a reference level
- » Creation of measurement profiles to be able to carry out recurring measurements with the same settings
- » Pinpoint listen-in including making ultrasound audible
- » Trigger function for automated recording when a level or frequency curve is exceeded
- » Create measurement series
- » Create photos and videos





Measurement of a humidifier: The openings for air circulation are clearly visible in the acoustic image.

Software

Modes Standard: Simplified mode for a quick start

Pro: Expert mode with extended range of functions

Leak: Optimized mode for the detection of leaks including **real**-

time display of the loss rate

Partial Discharge: Optimized mode for PD detection including real-time display of the PRPD diagram

Network: Remote control of the device via the Windows software

Functions Local and global spectrum (narrowband, 1/3rd octaves and octaves), spectrogram, acoustic, optical and thermal image

Setting the distance

Frequency filter (narrow band, 1/3rd octaves and octaves)

3 acoustic scaling modes: Smart, Auto, Manual

Pinpoint listen-in (broadband or frequency-filtered) incl. making ultrasound audible

Screenshot with comment option

Playback in real time, slow motion or frame by frame

Marking of events

Adjustment of window sizes

Project-based work via measurement series

Creation and management of **measurement profiles/modes**File manager for copying, moving, deleting, exporting and

rie manager for copying, moving, deleting, exporting and viewing files

Recording Ring buffer: 10 s, 30 s, 60 s and additionally on Windows 120 s, 180 s and 240 s

Trigger recording: SPL- or frequency-triggered up to 10 s with prerun plus post-run time

Long-term measurement: One image (average and peak hold) every 20 s to 900 s (adjustable)


Export Photo, video, audio, measurement data

Units Metric or imperial system

Languages German, English, Spanish, Croatian, Italian, Japanese, Korean, Polish, Turkish, Chinese, Czech

OS Linux (for the device), Windows (for laptop/PC)

Protection Password protection against unauthorized access



The thermal image shows warming of the control electronics in the center

Performance Well thought out to the last detail



- » Very high sensitivity and dynamic range thanks to 176 microphones with 200 kHz sampling rate at 24 bit resolution
- » Live, on-screen results at 100 acoustic fps
- » Precise synchronization between acoustic and optical video for high analysis accuracy
- » Built-in thermal imaging camera
- » High-resolution display with 1280 x 800 px and very good readability and high color transmission thanks to optical bonding




- » Ergonomic hand-held device with protection class IP54 waterproof
- » Can be used without prior knowledge thanks to intuitive software
- » Windows software for fast, detailed evaluation and reporting
- » Pinpoint listen-in, including making ultrasound audible, provides additional information
- » Optimum match of camera and display resolution through pixel-identical playback

Sensors Extremely sensitive



Result of the SoundCam 2.0, the predecessor model of the SoundCam 3. This is a very good acoustic camera with 64 microphones. The large leakage is detected very well. The small leakage is not detected as it disappears in the image noise.



The 176 microphones and the optimized microphone array design of the SoundCam 3 increase the sensitivity and dynamic range immensely. As a result, the large and small leaks are clearly visible. Even at 20 dB dynamic range, no image noise is visiable.

More microphones, a higher sampling rate and high 24-bit resolution ensure better, more detailed and more reliable results.





